

|                        |                                                                     |                                                                             |
|------------------------|---------------------------------------------------------------------|-----------------------------------------------------------------------------|
| <b>DNP</b>             | <b>TECHNICAL UPDATE NOTICE</b>                                      | <b>TUN-1708-01</b>                                                          |
| <b>Date:</b>           | AUG 30th, 2017                                                      | <b>Page:</b> 1 / 1                                                          |
| <b>Subject:</b>        | The release of DS-RX1 FW V2.06 and CSP Printer Status API V 0.6.8.5 |                                                                             |
| <b>Application on:</b> | DS-RX1                                                              | <b>Application mode:</b> <b>Immediately</b><br>As necessary<br>Periodically |

### DESCRIPTION:

This is to let you know the release of DS-RX1 FW V2.06 and CSP Printer Status API (commonly called "Direct DLL") V 0.6.8.5

### Release target and detail

#### 1) FW V2.06

**\*) This is only for sales companies or agencies that had technical training.**

The following files are included.

| FW file        | CWD data                                   |
|----------------|--------------------------------------------|
| DS-RX1_0206s.s | DS-RX1_300_0201.cwd<br>DS-RX1_300_0100.cwd |

\*) CWD data are the same ones in FW V2.05

- Added 5x5 and 6x6 sizes.

[Attention]

For printing with paper sizes 5x5 and 6x6,  
the application developed using "CSP Printer Status API version 0.6.8.5" is required.

#### 2) DS-RX1 Version up Tool for Firmware version 2.06

Please refer to the attached document in Version up Tool.

[Target OS]

Windows XP, Windows VISTA(32bit), Windows 7(32bit,64bit),  
Windows 8(32bit,64bit), Windows 8.1(32bit,64bit), Windows 10(32bit,64bit)

[Attention]

- When you use this tool, it is necessary that ".Net Framework 4.\*" is installed on the PC.

(The available version "\*" depends on each OS)

In Windows 8 and later, the .Net Framework is installed by the standard.

If ".Net Framework 4.\*" is not installed, Message box will be displayed when you start the upgrade tool. In the message box, choose "Install this feature" to install the ".NET Framework 4.\*".

Installing ".NET Framework 4.\*" requires an Internet connection.

#### 3) CSP Printer Status API (commonly called "Direct DLL") version 0.6.8.5

- Paper size 5x5 and 6x6 was supported. (for DS-RX1 firmware version 2.06 or later)
- L multi cut was supported. (for DS-RX1 firmware version 1.20 or later)
- Fine Matte was supported. (for DP-DS620 firmware version 1.52 or later)

[Attention]

- NDA between (sales company or DNPJ) and agency should be required.

Our sales can distribute above 1) and 2).

**Caution / Limitation;**

- DS-RX1 5x3.5x2 (multi-cut)  
Cutting scrap seldomly gets out from paper discharge port at low temperature. But any jamming doesn't occur.

\*) Regarding other items, please refer to the Release Note.

**Application;**

This FW will be applied to printer production.

We will inform you applied S/N with revised TUN.

**Attached file;**

- ReleaseNote\_DS-RX1 V206.pdf